

Product data sheet

Specifications



Orion - duplex American socket outlet 2P+E 15A 125V NEMA 5-15R with fixing frame

S703250045

⚠ Discontinued on: Dec 15, 2022

⚠ Discontinued

Main

Range Of Product	Orion
Range	Orion
Product Or Component Type	Socket-outlet
Device Presentation	Mechanism with fixing frame
Outlet Poles Configuration	2P + E without shutter
Fixing Mode	By screws
Type Of Packing	Flow-pack
Quantity Per Set	Set of 10
Sale Per Indivisible Quantity	1
Rated Current	15 A at 125 V AC 50/60 Hz

Complementary

Number Of Power Socket Outlets	2
Device Mounting	Flush
Outlet Standard	American
Ground Lug Position	Straight 0° position
Number Of Modules	3 modules 120 x 82.5 mm
Surface Finish	Glossy
Surface Treatment	Untreated
Ambient Air Temperature For Storage	-20...60 °C
Dielectric Strength	2000 V
Ambient Air Temperature For Operation	-5...35 °C
Electrical Durability	5000 cycles
Connections - Terminals	3 screw terminals
Screwdriver Shape	Philips
Number Of Cables	2
Clamping Connection Capacity	1.5...4 mm ² for rigid cable(s) 1.5...4 mm ² for stranded cable(s) 1.5...4 mm ² for flexible cable(s)
Wire Stripping Length	12 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Material	PA (polyamide): mechanism cover PA (polyamide): casing ABS (acrylonitrile butadiene-styrene): adaptor frame
Height	113 mm
Width	71 mm
Depth	29.1 mm
Embedding Depth	21 mm
Net Weight	0.105 kg
Standards	UL 498 NEMA 5-15R

Environment

Product Certifications	NOM
Ik Degree Of Protection	IK05
Ip Degree Of Protection	IP20
Environmental Characteristic	Petrol Alcohol Window-cleaning fluid Bleach Acetone Hydrogen peroxide (H2O2) Oil UV resistant Liquid soap

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.9 cm
Package 1 Width	9.3 cm
Package 1 Length	20.0 cm
Package 1 Weight	107.0 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation
