

# Product data sheet

Specifications



## Orion - blind cover 4X2 - horizon gold

S730100234

### Main

Range	Orion
Aesthetic Name	Orion Essence
Product Or Component Type	Blind cover

### Complementary

Device Mounting	Flush
Fixing Mode	Clip-in
Colour Tint	Horizon gold (Pantone 8381C)
Surface Finish	Matt
Surface Treatment	Painted
Type Of Packing	Flow-pack
Quantity Per Set	Set of 20
Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	-5...35 °C
Material	Thermoplastic ABS-UV stabilised: decorative frame
Height	120 mm
Width	82.5 mm
Depth	7.9 mm
Net Weight	0.0213 kg

### Environment

Ik Degree Of Protection	IK07
Ip Degree Of Protection	IP21D
Environmental Characteristic	Liquid soap Petrol Window-cleaning fluid UV resistant Hydrogen peroxide (H2O2) Oil Acetone Bleach Alcohol

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	0.8 cm
Package 1 Width	9.3 cm
Package 1 Length	20.0 cm
Package 1 Weight	23.0 g

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Eu Rohs Directive

Under investigation

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations