

Product data sheet

Specifications



Orion - cover-frame 4X2 - 3 modules - aluminium / chrome satin

S732103505

⚠ Discontinued on: Dec 15, 2021

⚠ Discontinued

Main

Range	Orion
Aesthetic Name	Orion materials chrome
Product Or Component Type	Cover frame

Complementary

Device Mounting	Flush
Number Of Gangs	1 gang
Number Of Modules	3 modules
Fixing Mode	Clip-in
Colour Tint	Gamma silver (RAL 9006) Chrome satin (Pantone 8402C)
Surface Finish	Glossy
Surface Treatment	Painted
Type Of Packing	Flow-pack
Quantity Per Set	Set of 10
Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	-5...35 °C
Material	Thermoplastic ABS-UV stabilised: decorative frame
Height	120 mm
Width	82.5 mm
Depth	8.3 mm
Net Weight	0.0221 kg

Environment

Ik Degree Of Protection	IK07
Ip Degree Of Protection	IP21D
Environmental Characteristic	Hydrogen peroxide (H2O2) Bleach Oil Liquid soap Alcohol Petrol Acetone Window-cleaning fluid UV resistant

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.8 cm
Package 1 Width	9.3 cm
Package 1 Length	20 cm
Package 1 Weight	24 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Under investigation
Circularity Profile	No need of specific recycling operations