

Product data sheet

Specifications



Orion - cover-frame 4X2 - 1 module - white / aluminium orbital blue

S733101615

⚠ Discontinued on: Sep 30, 2021

⚠ Discontinued

Main

Range	Orion
Aesthetic Name	Orion materials aluminium
Product Or Component Type	Cover frame

Complementary

Device Mounting	Flush
Number Of Gangs	1 gang
Number Of Modules	1 module
Fixing Mode	Clip-in
Colour Tint	White (RAL 9003) Aluminium orbital blue (Pantone 629C)
Surface Finish	Metallic
Surface Treatment	Metallic
Type Of Packing	Flow-pack
Quantity Per Set	Set of 10
Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	-5...35 °C
Material	Thermoplastic ABS-UV stabilised: decorative frame Metal
Height	120 mm
Width	82.5 mm
Depth	8.3 mm
Net Weight	0.0291 kg

Environment

Ik Degree Of Protection	IK07
Ip Degree Of Protection	IP21D

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental Characteristic	Window-cleaning fluid
	Bleach
	Oil
	UV resistant
	Liquid soap
	Alcohol
	Hydrogen peroxide (H2O2)
	Petrol
	Acetone

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.8 cm
Package 1 Width	9.3 cm
Package 1 Length	19 cm
Package 1 Weight	31 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Under investigation
Circularity Profile	No need of specific recycling operations