

# Product data sheet

Specifications



## Orion - cover-frame 4X2 - 1 module - white / aluminium venus pink

S733101625

⚠ Discontinued on: Dec 15, 2021

⚠ Discontinued

### Main

Range	Orion
Aesthetic Name	Orion materials aluminium
Product Or Component Type	Cover frame

### Complementary

Device Mounting	Flush
Number Of Gangs	1 gang
Number Of Modules	1 module
Fixing Mode	Clip-in
Colour Tint	White (RAL 9003) Aluminium venus pink (Pantone 8062C)
Surface Finish	Metallic
Surface Treatment	Metallic
Type Of Packing	Flow-pack
Quantity Per Set	Set of 10
Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	-5...35 °C
Material	Thermoplastic ABS-UV stabilised: decorative frame Metal
Height	120 mm
Width	82.5 mm
Depth	8.3 mm
Net Weight	0.0291 kg

### Environment

Ik Degree Of Protection	IK07
Ip Degree Of Protection	IP21D

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental Characteristic	Hydrogen peroxide (H2O2) Liquid soap Alcohol Acetone Oil Bleach Petrol UV resistant Window-cleaning fluid
------------------------------	---

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.8 cm
Package 1 Width	9.3 cm
Package 1 Length	19 cm
Package 1 Weight	31 g

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Under investigation
Circularity Profile	No need of specific recycling operations