

# Product data sheet

Specifications



## APC Parallel Maintenance Bypass for 2 UPS (1+1) 3:1 15-20kVA Wallmount

SBPAR3I15K20R2M2-WP

 **Discontinued on:** Oct 18, 2023

 **Discontinued**

### Overview

Lead Time Usually Ships within 4 Weeks

### Main

Main Input Voltage	400 V 3 phases
Main Output Voltage	220 V
Other Output Voltage	230 V
Output Connector Type	Hard wire 3-wire (H N + E) 1
Provided Equipment	Installation guide

### Physical

Height	120 cm
Width	101 cm
Depth	80 cm
Net Weight	100 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Rack-mounted

### Conformance

Standards	EN 50091-2 EN/IEC 62040-1-1 EN/IEC 62040-3 VFI-SS-111
-----------	--

### Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...9144.00 m

### Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	120 cm
Package 1 Width	101 cm
Package 1 Length	80 cm
Package 1 Weight	100 kg

## Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------