

# Product data sheet

Specifications



## APC Parallel Maintenance Bypass for 2 UPS (1+1) 3:1 30-40kVA Wallmount

SBPAR3I30K40R2M2WP

 **Discontinued on:** Feb 1, 2022

 **Discontinued**

### Overview

**Lead Time** Usually Ships within 4 Weeks

### Main

**Main Input Voltage** 400 V 3 phases

**Main Output Voltage** 220 V

**Other Output Voltage** 230 V

**Output Connector Type** Hard wire 3-wire (H N + E) 1

**Provided Equipment** Installation guide  
User manual

### Physical

**Colour** Black

**Height** 139 cm

**Width** 101 cm

**Depth** 41.5 cm

**Net Weight** 123 kg

**Mounting Location** Front

**Mounting Preference** No preference

**Mounting Mode** Not rack-mountable

### Input

**Network Frequency** 50 Hz

### Conformance

**Standards** EN 50091-2  
EN/IEC 62040-1-1  
EN/IEC 62040-3  
VFI-SS-111

### Environmental

**Ambient Air Temperature For Operation** 0...40 °C

**Relative Humidity** 0...95 %

**Operating Altitude** 0...10000 ft

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	-15...40 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...9144.00 m

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	139 cm
Package 1 Width	101 cm
Package 1 Length	41.5 cm
Package 1 Weight	123 kg

## Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------