


Product data sheet

Specifications



Sedna - double socket outlet with pin earth - 16A shutters, cream, CZ std

SDN2890523

 **Discontinued on:** Nov 20, 2017

 **Discontinued**

Main

Range	Sedna
Product Or Component Type	Socket-outlet
Outlet Standard Description	Pin earth
Delivery Form	Complete product
Additional Features	Shuttered
Outlet Standard	Czech Republic Slovakia
Rated Current	16 A at 250 V AC
Cover Plate Color	Cream
Kind Of Terminals	Lift terminals

Complementary

Installation	Flush
Power Range	3680 W
Terminal Capacity	2 cable(s) 2.5 mm²
Wire Structure	Solid stranded Rigid Flexible
Wire Stripping Length	11 mm
Material Of Visible Parts	ASA + PC
Surface Finish	Glossy
Fixing Mode	Screws or claws 55...75 mm
Height	120 mm
Width	84 mm
Depth	44 mm
Depth Of Visual Part	20.3 mm
Net Weight	0.0978 kg

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.4 cm
Package 1 Width	8.4 cm
Package 1 Length	12 cm
Package 1 Weight	98 g

Contractual warranty

Warranty	18 months
----------	-----------