

# Product data sheet

Specifications



## Easy UPS 1 Ph On-Line SRVS Tower Battery Pack for 6/10kVA Extended runtime model, 240V

SRVS240BP-9A

### Overview

Lead Time	Usually in Stock
-----------	------------------

### Main

Product Or Component Type	Uninterruptible power supply (UPS)
Battery Type	Lead-acid battery
Provided Equipment	User manual Battery cable

### Batteries & Runtime

Number Of Battery Blocks Per String	20
Device Mounting	Floor mounted
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Voltage	240 V

### Physical

Colour	Black
Height	36.8 cm
Width	19 cm
Depth	48.5 cm
Net Weight	60 kg
Mounting Mode	Not rack-mountable
Usb Compatible	No

### Conformance

Product Certifications	CE UKCA EAC EN/IEC 62040-1
------------------------	-------------------------------------

### Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 % non-condensing
Operating Altitude	0...3000 m

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	-15...40 °C
Storage Relative Humidity	0...95 % non-condensing
Storage Altitude	0...15000 m

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	47.000 cm
Package 1 Width	32.000 cm
Package 1 Length	56.500 cm
Package 1 Weight	63.866 kg

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>