

Product data sheet

Specifications



APC Smart-UPS Hardwire Kit for 2200/3000/5000VA SUA models, 120/208/230V

SUA031

Overview

Presentation	Accessory solutions to tailor the Smart-UPS to meet your specific needs.
Lead Time	Usually in Stock

Main

Main Input Voltage	120 V 208 V 230 V
Product Or Component Type	Kit
Main Output Voltage	120 V 208 V 230 V
Provided Equipment	Hardwire panel Installation guide

Physical

Height	12.7 cm
Width	17.8 cm
Depth	5.1 cm
Net Weight	0.91 kg
Mounting Location	Rear
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Usb Compatible	No

Input

Max Line Current	30 A
------------------	------

Output

Max Current Draw	30 A
------------------	------

Conformance

Product Certifications	cUL recognized UL recognized
------------------------	---------------------------------

Environmental

Ambient Air Temperature For Operation	0...40 °C
---------------------------------------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Relative Humidity	0...95 %
Ambient Air Temperature For Storage	-15...45 °C
Storage Relative Humidity	0...95 %

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.7 cm
Package 1 Width	17.8 cm
Package 1 Length	25.4 cm
Package 1 Weight	1.357 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Take-back Transparency RoHS/REACH

Resource performance

✓ Take-Back Program Available

Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile