

# Product data sheet

Specifications



## Ulti - 250V 16 AX 1 gang 1-way impress switch module, blue LED

U201SPM-1\_B00

### Main

|                           |               |
|---------------------------|---------------|
| Range                     | Ulti          |
| Product Or Component Type | Switch module |
| Load Type                 | Fluorescent   |
| Switch Application        | Switch        |

### Complementary

|                          |                         |
|--------------------------|-------------------------|
| Bulb Type                | LED blue                |
| Rated Current            | 16 AX at 250 V AC 50 Hz |
| Number Of Cables         | 3 cable(s) 2.5 mm²      |
| Opening Distance         | > 3 mm                  |
| Device Mounting          | Flush                   |
| Fixing Mode              | By screws               |
| Distance Between Centers | 60.3 mm                 |
| Number Of Gangs          | 1 gang                  |
| Switch Function          | 1-way                   |
| Width                    | 87 mm                   |
| Height                   | 87 mm                   |
| Depth                    | 23.3 mm                 |

### Environment

|                                       |                 |
|---------------------------------------|-----------------|
| Ambient Air Temperature For Operation | 0...35 °C       |
| Relative Humidity                     | 0...95 %        |
| Standards                             | BS EN 60669-1   |
| Environmental Characteristic          | No UV resistant |
| Operating Altitude                    | <= 2000 m       |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications