

Product data sheet

Specifications



Actassi 19-C Patch Panel Sliding Basic 19" 1U 24pt SLIM FTP/STP Empty

VDIG012241F

Main

Range Of Product	Actassi
Product Or Component Type	Empty sliding 19" data panel
Device Presentation	Empty
Provided Equipment	2 quick fix 19" mountings
Colour	Dark grey (RAL 7016)
Additional Information	Automatic grounding

Complementary

Variant	Basic
Number Of Port	24 port of FTP/STP
Communication Network Category	5e 6 _A 6
Cover Type	Screened
Mounting Support	19" rack
Number Of Rack Unit	1U
Type Of Connector	S-One
Material	DC01 metal sheet 1.2 mm PA6 plastic part PA66 GF20 plastic part
Width	490 mm
Depth	230 mm
Height	47 mm
Net Weight	2.2 kg

Environment

Ambient Air Temperature For Operation	-10...55 °C
Standards	IEC 60297 ISO/IEC 11801:ed. 2.2, 2011 NF C 20-150

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	26.8 cm
Package 1 Length	54.8 cm
Package 1 Weight	2.037 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	6
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	13.008 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	36
Package 3 Height	100 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	90.048 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations