

Product data sheet

Specifications

Actassi 19-C Patch Panel Fixed Evo 19" 1U 24pt S-110 UTP Empty



VDIG113241U

Main

Range of product	Actassi
Product or component type	Empty fixed 19" data panel
Device presentation	Empty
Provided equipment	4 label holders 2 quick fix 19" mountings Ports identification at the rear 1 removable cable tray
Colour	Dark grey (RAL 7016)
Additional information	Cable organiser Connector release tool

Complementary

Variant	Evolution
Number of port	24 port of UTP
Communication network category	6 5e
Mounting support	19" rack
Number of rack unit	1U
Type of connector	S-110 keystone
Material	DC01 metal sheet 1.5 mm PA66 GF20 plastic part PC plastic part
Width	484 mm
Depth	190 mm
Height	44 mm
Net weight	1 kg

Environment

Ambient air temperature for operation	-10...55 °C
Standards	IEC 60297 NF C 20-150

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	19.5 cm
Package 1 Length	50.5 cm
Package 1 Weight	1.059 kg
Unit Type of Package 2	S04
Number of Units in Package 2	7
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	8.179 kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)