


Product data sheet

Specifications

Actassi 19-C Patch Panel Fixed Evo 19" 1U 24pt S-110 UTP Empty



VDIG113241U

 **Discontinued on:** Aug 31, 2023

 **Discontinued**

Main

Range Of Product	Actassi
Product Or Component Type	Empty fixed 19" data panel
Device Presentation	Empty
Provided Equipment	4 label holders 2 quick fix 19" mountings Ports identification at the rear 1 removable cable tray
Colour	Dark grey (RAL 7016)
Additional Information	Cable organiser Connector release tool

Complementary

Variant	Evolution
Number Of Port	24 port of UTP
Communication Network Category	6 5e
Mounting Support	19" rack
Number Of Rack Unit	1U
Type Of Connector	S-110 keystone
Material	DC01 metal sheet 1.5 mm PA66 GF20 plastic part PC plastic part
Width	484 mm
Depth	190 mm
Height	44 mm
Net Weight	1 kg

Environment

Ambient Air Temperature For Operation	-10...55 °C
Standards	IEC 60297 NF C 20-150

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	6.5 cm
Package 1 Width	19.5 cm
Package 1 Length	50.5 cm
Package 1 Weight	1.059 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	7
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	8.179 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile		No need of specific recycling operations