

# Product data sheet

Specifications



## Actassi 19-C Panel 19" 1U for Horizontal Patch Cord Guiding



VDIG188141

### Main

Range	LexCom
Product	19" patchcord guiding panel
Colour	Light grey (RAL 7035) Dark grey (RAL 7016)
Provided equipment	2 quick fix 19" mountings
Additional features	4 openable rings

### Complementary

Rack unit	1U
Material	Metal sheet: DC01 Plastic part: PA66 GF20 Plastic part: PC
Width	490 mm 0.49 m
Height	45 mm 0.04 m
Depth	100 mm 0.10 m

### Environment

Ambient air temperature for operation	-10...55 °C -10...55 °C
Standards	IEC 60297 NF C 20-150

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	506 g
Package 1 Height	5.5 cm
Package 1 width	16 cm
Package 1 Length	51.7 cm
Unit Type of Package 2	S04
Number of Units in Package 2	11

Package 2 Weight	6.249 kg
Package 2 Height	30 cm
Package 2 width	40 cm
Package 2 Length	60 cm
Package 3 Height	50 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

## Contractual warranty

Warranty	18 months
----------	-----------