

Product data sheet

Specifications



Actassi - trunk 1x12 MTP/1x12 MTP - OM4 - Euroclass C

VDILL044C4C0

 **Discontinued on:** Feb 10, 2021

 **Discontinued**

Main

Range	Actassi
Product Or Component Type	Trunk
Colour	MTP connector: magenta Sheath: magenta
Type Of Packing	50...500 m cable drum

Complementary

Optic Fibre Type	Loose tube
Maximum Insertion Loss	0.5 dB 850 nm
Minimum Return Loss	20 dB 850 nm
Fibre Performance	OM4
Optic Fiber Diameter	250 µm
Sheath Type	Standard
Condition Of Use	Indoor
Cable Outer Diameter	3 mm
Material	Plastic: MTP connector
Cable Length	1...500 m
Targeted Region	Europe

Environment

Ambient Air Temperature For Operation	-10...60 °C
Ambient Air Temperature For Storage	-25...70 °C
Euroclass Level	C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards

Fibre performance: ITU G.651
Cable specification: IEC 60794-2
Cable test procedure: IEC 60794-1-2
Flame retardance: IEC 60332-1
IEC 60754-1
Acidity of combustion gases: IEC 60754-2
Smoke generation: IEC 61034
MTP connector: IEC 61754-7
MTP connector: TIA/EIA-604-5
Performance: ISO/IEC 11801:2011 Ed.2.2
Cabling: ISO/IEC 24764
Fibre cabling test: ISO/IEC 14763-3
TIA/EIA-568-C.3
ANSI/TIA-942
10Gbase-SR: IEEE 802.3ae
Fibre performance: IEC 60793-2-10 Type A1a.3