

# Product data sheet

Specifications



## Actassi 19-DC Patching Frame Overhead 19" 4U

VDIM33174

### Main

Range Of Product	Actassi
Product Or Component Type	19" uprights
Device Application	Overhead patching
Number Of Units 19" - Height	4U - 350 mm
Installation Mode	Cable ladder mounted Tray mounted Overhead
Applications	To mount 19" equipment
Enclosure Type	Open frame
Colour	Uprights: raven black

### Complementary

Device Composition	2 x 19" uprights
Load Rating	15 kg static
Support Equipment	2 x 19" uprights (vertical) 4 x mounting bracket (angled) 4 x bolts and nuts 4 x cord self-lock grip strip 2 x cord manager 1 x label holder
Material	Steel
Surface Finish	Epoxy-polyester powder
Width	500 mm
Depth	160 mm

### Environment

Standards	EIA-310D IEC 60297-3-100
-----------	-----------------------------

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.000 cm
Package 1 Width	26.000 cm
Package 1 Length	54.000 cm
Package 1 Weight	2.802 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	S04
Number Of Units In Package 2	4
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	11.695 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	48
Package 3 Height	75.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	140.340 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations