

Product data sheet

Specifications



Actassi CL-MNC patch cord, F/UTP, 4P, category 5e, 155 MHz, LSZH, 1 m, grey

VDIP184546010

! To be discontinued on: 16 December 2021

! To be end-of-service on: 16 December 2021

! To be discontinued

Main

Range	Actassi
Product	Patch cord
Colour	Patchcord: grey
Quantity per set	1
Cable shielding type	F/UTP
Provided component	Grey coloured clips Green coloured clips Red coloured clips

Complementary

Product compatibility	Coloured clips red Coloured clips green Coloured clips yellow Coloured clips blue
Length (customizable value in configurator)	0...1 m
Communication network type	10GBASE-T
Connector type	RJ45
Communication network category	5e
Transmission frequency	155 MHz
AWG gauge	AWG 26
Input impedance	100 Ohm
Material	Solid bare copper: conductor PE (polyethylene): wire insulation
Targeted region	Europe

Environment

Ambient air temperature for installation	0...50 °C
Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-20...60 °C

Temperature resistance	60 °C
Flame retardance	LSZH
Product certifications	Delta
Standards	EIA/TIA-568-C.2 ISO/IEC 11801:2011 Ed.2.2 EN 50173 Ed.3 IEC 61935-2

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	47 g
Package 1 Height	1.2 cm
Package 1 width	20.5 cm
Package 1 Length	25 cm
Unit Type of Package 2	S03
Number of Units in Package 2	100
Package 2 Weight	5.268 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)

VDIP184546010 is replaced by:

1x



Patch cord, Actassi, Category 6, F/UTP, LSZH, 1 m, white
ACTPC6FULS10WE