


# Product data sheet

Specifications



## LexCom Home Premium - IR110 IR receiver + emitter - black

VDIR672104

 **Discontinued on:** Dec 31, 2018

 **Discontinued**

### Main

Range	LexCom Home
Product Name	LexCom Home Premium
Product Type	IR receiver + emitter
Commercial Name	IR110

### Complementary

Operating Distance	<= 8 m
Connector Type	2.5 mm jack
Bandwidth	35...55 kHz
Output Impedance	100 Ohm
Shield Attenuation	55 dB
Material	Die cast zinc
Detection Angle	50°
Surface Finish	Chrome plated
Colour Tint	Receiver: black
Cable Length	2.8 m for emitter 2.8 m for receiver
Height	Receiver: 9 mm
Width	Receiver: 19 mm
Depth	Receiver: 58 mm
Net Weight	0.028 kg emitter 0.071 kg receiver

### Environment

Standards	EMC directive EN 55020
-----------	---------------------------

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	8.2 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	11.3 cm
Package 1 Weight	0.12 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Certifications & Standards

**Eu Rohs Directive**

Compliant

[EU RoHS Declaration](#)

**Environmental Disclosure**

[Product Environmental Profile](#)