

Product data sheet

Specifications



LexCom Home Premium - B100 tele adaptor

VDIR673001

 **Discontinued on:** Nov 21, 2018

 **Discontinued**

Main

Range	LexCom Home
Product Name	LexCom Home Premium
Product Type	Tele adaptor
Commercial Name	B100
Equipment Provided	2 x 0.5 m RJ11/RJ11 cable 0.5 m RJ11/RJ45 cable

Complementary

Connector Type	2 port(s) RJ11 - cable shielding type: U/UTP for input 1 port(s) RJ45 - cable shielding type: U/FTP for input 1 port(s) RJ45 - cable shielding type: U/FTP for output
Material	PC/ABS: housing
Colour Tint	Black
Height	78 mm
Width	40 mm
Depth	22 mm
Weight	0.04 kg

Environment

Temperature Range	0...45 °C
Relative Humidity	5...95 %
Standards	IEC 512-2 : 1985

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.8 cm
Package 1 Width	3.8 cm
Package 1 Length	2.2 cm
Package 1 Weight	106 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)