

Product data sheet

Specifications



Roda - USB charger 2.0 - 1A 127/220V - 1 module - graphite

WDA65812

Main

Range Of Product	Roda
Product Or Component Type	USB charger
Fixing Mode	Fixed
Integrated Connection Type	1 USB port 5 V DC, maximum load current: 1 A

Complementary

Device Mounting	Flush
Device Presentation	Mechanism
Range Compatibility	Roda fixing frame
Colour Tint	Grey
Surface Finish	Matt
Surface Treatment	Untreated
Number Of Modules	1 module
Type Of Packing	Flow-pack
Quantity Per Set	Set of 8
Sale Per Indivisible Quantity	1
Ambient Air Temperature For Operation	0...40 °C
Ambient Air Temperature For Storage	-5...50 °C
Relative Humidity	15...95 %
Connector Type	USB 2.0
[Ue] Rated Operational Voltage	127/250 V AC at 50/60 Hz
Power Consumption In W	0.1 W
Input Power	5 W
Material	Thermoplastic ABS-UV stabilised: centre plate PC (polycarbonate) GF10 FR: casing PC (polycarbonate): centre plate
Protection Type	Short time short-circuit protection
Number Of Terminals	2 screw terminals
Screwdriver Shape	Phillips combined
Clamping Connection Capacity	1.5...2.5 mm² for flexible cable(s) 1.5...2.5 mm² for rigid cable(s)
Wire Stripping Length	7 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Compatibility	Apple Emblaze mobile Nokia Sony Ericsonn Research in Motion Qualcomm Atmel LGE Huawei Technologies Samsung Texas Instruments Motorola Mobility TCT mobile (ALCATEL)
Height	43 mm
Width	23 mm
Depth	45 mm
Embedding Depth	42 mm
Net Weight	0.05 kg

Environment

Standards	EN 60950-1 NEMA 5-15R EN 62684 ETSI EN 300 489-34
Directives	2004/108/EC - electromagnetic compatibility 2006/95/EC - low voltage directive 2009/125/EC - ecodesign
Electrical Insulation Class	Class II
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP20
Environmental Characteristic	Alcohol Acetone UV resistant Petrol Bleach Liquid soap Hydrogen peroxide (H2O2) Window-cleaning fluid Oil

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.3 cm
Package 1 Width	2.3 cm
Package 1 Length	4.5 cm
Package 1 Weight	0.025 kg
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	2.5 cm
Package 2 Width	10.5 cm
Package 2 Length	15 cm
Package 2 Weight	620 g

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information