

Product data sheet

Specifications



Roda - Light rotary Dimmer - 127/220V - Ivory

WDA95013

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	Roda
Product Or Component Type	Dimmer
Colour Tint	Ivory

Complementary

Device Presentation	Mechanism
Control Type	Rotary
Type Of Packing	Group
Device Application	Lighting
[Ue] Rated Operational Voltage	127...220 V AC 50/60 Hz
Power Range	230 V AC incandescent lamp: 400 W 127 V AC halogen lamp: 200 W 230 V AC halogen lamp: 400 W 127 V AC incandescent lamp: 200 W 230 V AC LED lamp: 100 W 127 V AC LED lamp: 50 W
Material	ABS + PC
Number Of Modules	1 module
Depth	39 mm
Height	25 mm
Width	45 mm
Connections - Terminals	Pre-stripped wire terminations
Fixing Mode	Clip-in

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	10.7 cm
Package 1 Length	16 cm
Package 1 Weight	35 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	6

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	9 cm
Package 2 Width	14 cm
Package 2 Length	12.5 cm
Package 2 Weight	223 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation
