

Product data sheet

Specifications



Exxact push-dimmer universal 400W/VA metallic

WDE004307

Discontinued on: Mar 29, 2021

Discontinued

Main

Range	Exxact
Product Or Component Type	Dimmer
Colour Tint	Metallic
Quantity Per Set	Set of 1

Complementary

Device Presentation	Mechanism with fixing frame
Device Mounting	Flush
Device Application	Light control
Switch Function	1-pole 2-way
Dimmer Type	Universal
Dimmer Control	Push type
Fixing Mode	By screws
Rated Current	10 A
[Ue] Rated Operational Voltage	230 V
Network Type	AC
Network Frequency	50 Hz
Surface Finish	Painted
Load Type	Motor (single-phase): 20...200 W at 230 V AC Incandescent lamp: 20...400 W at 230 V AC Halogen lamp: 20...400 W at 230 V AC Conventional transformer: 20...400 W at 230 V AC Electronic transformer: 20...400 W at 230 V AC Toroidal transformer: 20...300 W at 230 V AC
Connections - Terminals	Screw terminals
Shape Of Screw Head	Pozidriv No 1 and combi
Tightening Torque	0.5 N.m
Clamping Connection Capacity	1 x 1.5...2 x 2.5 mm ² for solid cable(s) 1 x 1.5...2 x 2.5 mm ² for solid stranded cable(s)
Wire Stripping Length	6 mm
Material	ABS (acrylonitrile butadiene-styrene)
Height	71 mm
Width	71 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Embedding Depth	32 mm
Product Certifications	FIMKO SEMKO CE NEMKO

Environment

Ip Degree Of Protection	IP20 IP44 with additional sealing kit
Ik Degree Of Protection	IK02
Standards	EN 60669-2-1 EN 60669-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.6 cm
Package 1 Width	7.1 cm
Package 1 Length	7.1 cm
Package 1 Weight	1 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations