

Product data sheet

Specifications



monobloc sprocket with keyed
through hub - 12.7 mm pitch - 24
teeth - shaft Ø 55

XR2AZ42435

⚠ Discontinued on: Jan 12, 2022

⚠ Discontinued

Main

Range Of Product	XR
Accessory / Separate Part Designation	Monobloc sprocket with keyed through hub
Accessory / Separate Part Type	Winch shaft chain sprocket
Accessory / Separate Part Category	Separate parts
Accessory / Separate Part Destination	Screw limit switch

Complementary

Number Of Teeth	24
Chain Pitch	12.7 mm
Bore Diameter For Shaft	26...35 mm
Shaft Diameter	55 mm
External Diameter	105 mm
Pinion Length	35 mm

Environment

Standards	NF E 23-111
-----------	-------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications