

# Product data sheet

Specifications



## XR, potentiometer, 10000 Ohm, ball bearing mounting

XRZ9100

⚠ Discontinued on: Apr 5, 2022

⚠ Discontinued

### Main

Range Of Product	XR
Accessory / Separate Part Designation	Potentiometer
Accessory / Separate Part Type	Potentiometer
Accessory / Separate Part Category	Separate parts
Accessory / Separate Part Destination	Screw limit switch

### Complementary

Product Compatibility	XRBA
Potentiometer Characteristic	SI, size 15, ball bearing mounted
Maximum Rotation Angle Of Potentiometer	350 °
Power Consumption In W	3 W
Ohmic Value	10000 Ohm
Net Weight	0.06 kg

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.6 cm
Package 1 Width	6.3 cm
Package 1 Length	5.8 cm
Package 1 Weight	64 g

### Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
California Proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>