

# Product data sheet

Specifications



Complete pre wired monolithic tower light, Harmony XVC, plastic, red, 60mm, tube mounting, steady or flashing, buzzer, IP23, 100...240V AC

XVC6M15S

## Main

Range Of Product	Harmony XVC6
Product Or Component Type	Complete pre-wired monolithic tower light
Beacon Or Indicator Bank Unit Type	1 illuminated unit
Sound Signalling	Buzzer
Mounting Diameter	60 mm
Component Name	XVC
Light Source	LED steady or flashing red
[Us] Rated Supply Voltage	100...240 V
Supply Circuit Type	AC
Noise Level	70...85 dB (continuous or intermittent tone) at 1 m

## Complementary

Material	Polycarbonate: illuminated unit ABS (acrylonitrile butadiene-styrene): base unit PBT + ABS (UL94-V0): top cover
Product Mounting	On support tube, 22 mm
Cable Cross Section	0.83 mm² 0.33 mm²
Awg Gauge	AWG 22 AWG 18
Cable Length	450 mm
Marking	CE
[Uimp] Rated Impulse Withstand Voltage	4 kV
Current Consumption	60 mA
Fundamental Frequency	2.23 kHz
Flashing Frequency	1 Hz
Net Weight	1.01 kg
Height	599.8 mm

## Environment

Standards	IEC 60947-1 IEC 60947-5-1
Product Certifications	UL

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Protective Treatment	TC
Ambient Air Temperature For Storage	-35...70 °C
Ambient Air Temperature For Operation	-10...50 °C
Electrical Shock Protection Class	Class I conforming to IEC 61140
Ip Degree Of Protection	IP23 vertical surface installation conforming to IEC 60529

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.700 cm
Package 1 Width	8.700 cm
Package 1 Length	77.000 cm
Package 1 Weight	950.000 g
Unit Type Of Package 2	P06
Number Of Units In Package 2	10
Package 2 Height	75.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	18.000 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile

[End of Life Information](#)

California Proposition 65


WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

Dimensions Drawings

Pre-assembled and Pre-wired Tower Light with Support Tube Mounting

Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get **b1** dimension.



No. of illuminated units	b1 With buzzer (mm)	b1 With buzzer (in.)
1 stage	599.8	23.61
2 stages	639.8	25.19
3 stages	679.8	26.76
4 stages	719.8	28.34
5 stages	759.8	29.91

## Mounting and Clearance

### Pre-assembled and Pre-wired Tower Light

## Support Tube Mounting

