

Product data sheet

Specifications



BLUE STROBE/OFF-WHITE RING 0.3J 24VAC/DC

XVPC6B6W

⚠ Discontinued on: Jun 30, 2015

⚠ End-of-service on: Dec 31, 2015

⚠ Discontinued

Main

Range Of Product	Harmony XVP Universal
Product Or Component Type	Indicator bank
Beacon Or Indicator Bank Unit Type	Illuminated unit with cream clamping ring
Signalling Type	Flashing
Mounting Diameter	50 mm
Component Name	XVPC
Material	Polycarbonate and polyamide
Light Source	Integral flash discharge tube, blue
Bulb Type	Flash discharge tube
[Us] Rated Supply Voltage	24 V AC/DC
Flash Energy	1 J

Complementary

Assembly Style	Customer assembly, up to 5 units
Connections - Terminals	Screw clamp terminals, <= 1 x 1.5 mm ² with cable end
Marking	CE
[Ui] Rated Insulation Voltage	250 V conforming to IEC 60947-1
Nominal Voltage Limit	0.85...1.1 Un conforming to IEC 60947-5-1
Current Consumption	<= 100 mA AC/DC
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60947-1
Flashing Frequency	0.6...2 Hz
Service Life In Hours	1000 h at -25...50 °C
Cad Overall Width	56 mm
Cad Overall Height	65 mm
Cad Overall Depth	56 mm
Net Weight	0.12 kg

Environment

Product Certifications	cULus
Standards	EN/IEC 60947-5-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Protective Treatment	TC
Ambient Air Temperature For Storage	-40...70 °C
Electrical Shock Protection Class	Class I on support tube conforming to IEC 61140 Class II on base unit conforming to IEC 61140
Ip Degree Of Protection	IP65 conforming to IEC 60529

Contractual warranty


Warranty	18 months
----------	-----------

Dimensions Drawings

Indicator Bank without Audible Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get **b** dimension.



Number of illuminated units	b in mm	b in in.
1	108	4.25
2	170	6.69
3	232	9.13
4	294	11.57
5	356	14.02