

Product data sheet

Specifications



Joystick station, Harmony eXLhoist, joystick, 3 axes, 2 steps

ZARTJ2S3

 **Discontinued on:** Mar 31, 2023

 **Discontinued**

Main

Range Of Product	Harmony eXLhoist
Product Or Component Type	Joystick station
Device Short Name	ZARTJ
Control Button Type	2 configurable auxiliary push-button 2 non-configurable joystick 2 configurable selector switch

Complementary

Product Specific Application	Hoisting applications
Material	Enclosure: PP (polypropylene)
Display Type	LCD display 45 x 15 mm
Operating Distance	50 m
Communication Network Type	Wireless
Transmission Frequency	433 MHz
Maximum Sensing Distance	100 m in free field
Response Time	< 500 ms at full duplex
Charging Time	10800 s
Autonomy	16 h rechargeable
Mechanical Durability	1000000 cycles
Service Life	2 year(s)
Width	210 mm
Height	140 mm
Depth	130 mm
Net Weight	1.2 kg

Environment

Ip Degree Of Protection	IP65
Ambient Air Temperature For Operation	-20...55 °C
Ambient Air Temperature For Storage	-20...45 °C
Operating Altitude	0...2000 m
Storage Altitude	0...3000 m

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Relative Humidity	0...95 % at -20...60 °C operating
Product Certifications	CE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.5 cm
Package 1 Width	27.0 cm
Package 1 Length	19.0 cm
Package 1 Weight	1.668 kg

Dimensions Drawings

Dimensions

