

Product data sheet

Specifications



Head for non illuminated push button, Harmony XB5, XB4, blue flush pushbutton Ø22 mm spring return unmarked

ZB5APA6

! Discontinued

! Discontinued on: Mar 31, 2023

! End-of-service on: Apr 15, 2023

Main

| | |
|---------------------------------|--------------------------------------|
| Range Of Product | Harmony XB5 |
| Product Or Component Type | Head for non-illuminated push-button |
| Device Short Name | ZB5 |
| Product Compatibility | Not compatible with legend holder |
| Bezel Material | Dark grey plastic |
| Mounting Diameter | 22 mm |
| Head Type | Standard |
| Sale Per Indivisible Quantity | 1 |
| Shape Of Signaling Unit Head | Round |
| Type Of Operator | spring return |
| Operator Profile | Blue flush, unmarked |
| Operator Additional Information | Clear boot |

Complementary

| | |
|-----------------------|-----------------|
| Cad Overall Width | 30 mm |
| Cad Overall Height | 30 mm |
| Cad Overall Depth | 37 mm |
| Mechanical Durability | 10000000 cycles |
| Device Presentation | Basic element |

Environment

| | |
|---------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| Protective Treatment | TH |
| Ambient Air Temperature For Storage | -40...70 °C |
| Ambient Air Temperature For Operation | -40...70 °C |
| Overvoltage Category | Class II conforming to IEC 60536 |
| Ip Degree Of Protection | IP66 conforming to IEC 60529 IP67 conforming to IEC 60529 IP69 conforming to IEC 60529 IP69K conforming to ISO 20653 |
| Nema Degree Of Protection | NEMA 13 NEMA 4X |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Resistance To High Pressure Washer | 7000000 Pa at 55 °C, distance : 0.1 m |
| Ik Degree Of Protection | IK03 conforming to IEC 50102 |
| Product Certifications | LROS (Lloyds register of shipping) UL listed BV CSA DNV GL |
| Shock Resistance | 30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27 50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27 |
| Vibration Resistance | 5 gn (f= 2...500 Hz) conforming to IEC 60068-2-6 |

Packing Units

| | |
|------------------------------|--------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 4.5 cm |
| Package 1 Width | 3.4 cm |
| Package 1 Length | 4.4 cm |
| Package 1 Weight | 21.0 g |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|---------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |