

## EasyPact Power loss and impedance

	Rating (A)	Impedance	Power loss	
		1 pole (milliohms)	1 pole (W)	3 poles (W)
<b>EZC100</b>	15	11	3	8
	20	9.8	4	12
	25	9.5	6	18
	30	2.5	2	7
	40	2.2	4	11
	50	1.6	4	12
	60	1.4	5	16
	75	1.2	7	21
	80	1.2	8	24
100	1.0	10	30	
<b>EZC250</b> Depth 60mm MCCB	100	0.90	9	27
	125	0.55	9	26
	150	0.47	11	32
	160	0.47	12	36
	175	0.38	12	35
	200	0.30	12	36
	225	0.24	12	36
	250	0.21	13	39
<b>EZC250</b> Depth 68mm MCCB	63	1.08	4.3	12.9
	80	1.08	6.9	20.7
	100	0.90	9	27.0
	125	0.56	9	26
	150	0.49	11	33
	160	0.39	10	30
	175	0.39	12	36
	200	0.31	12	37
	225	0.24	12	36
250	0.21	13	39	
<b>EZCV250</b> Depth 68mm ELCB	63	1.10	4.4	13.1
	80	0.96	6.1	18.4
	100	0.63	6.3	18.9
	125	0.50	8	23
	150	0.40	9	27
	160	0.40	10	31
	175	0.34	10	31
	200	0.30	12	36
	225	0.23	12	35
250	0.21	13	39	
<b>EZC400</b>	250	0.24	15	45
	300	0.2	18	54
	320	0.18	18	55
	350	0.18	22	66
	400	0.17	27	82