
Product datasheet



Schneider 03032 Product picture Schneider

Electric



MOUNTING PLATE NSX 250 HZ. FIX+MOT/PLUG-IN

03032

! Discontinued on: 15 Jun 2023

Price: 897.59 ZAR

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure
Installation Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Floor-standing enclosure + duct - width 600 + 300 mm Wall-mounted enclosure + duct - width 600 + 300 mm
Installed Device	ComPact: fixed INS250 - control: lateral handle - vertical installation ComPact: fixed INV250 - control: lateral handle - vertical installation ComPact: fixed NSX100160 without earth leakage protection - control: motor mechanism - horizontal installation ComPact: plug-in NSX100160 without earth leakage protection - control: toggle - horizontal installation ComPact: fixed NSX250 without earth leakage protection - control: motor mechanism - horizontal installation ComPact: plug-in NSX250 without earth leakage protection - control: toggle - horizontal installation
Poles Description	1 x 3P: fixed NSX100160 horizontal installation 1 x 4P: fixed NSX100160 horizontal installation 1 x 3P: fixed NSX250 horizontal installation 1 x 4P: fixed NSX250 horizontal installation 1 x 3P: fixed INS250 vertical installation 1 x 4P: fixed INS250 vertical installation 1 x 3P: fixed INV250 vertical installation 1 x 4P: fixed INV250 vertical installation 1 x 4P: fixed INV250 vertical installation 1 x 4P: plug-in NSX100160 horizontal installation 1 x 4P: plug-in NSX100160 horizontal installation 1 x 3P: plug-in NSX250 horizontal installation 1 x 4P: plug-in NSX250 horizontal installation
Condition Of Using Cable Tie	Need additional plate (2M high) when installation of device is in horizontal Need additional plate (1M high) when installation of device is in vertical

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Number Of Vertical Modules [50 Mm]

4 module(s): NSX100...160 without earth leakage protection , direct with long terminal shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from top or bottom of enclosure)

4 module(s): NSX100...160 without earth leakage protection , direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from top or bottom of enclosure)

4 module(s): NSX250 without earth leakage protection , direct with long terminal shield in 600 + 300 mm Widefloor-standing enclosure + duct (cable coming from top or bottom of enclosure)

4 module(s): NSX250 without earth leakage protection , direct with long terminal shield in 600 + 300 mm Widewall-mounted enclosure + duct (cable coming from top or bottom of enclosure)

8 module(s): INS250, direct with long terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)

8 module(s): INS250, direct with long terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)

8 module(s): INV250, direct with long terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)

8 module(s): INV250, direct with long terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)

Standards IEC 61439-2
Product Certifications ASEFA

Complementary

Cable Entry	Cut-out plates 0.31 mm top or bottom 42 mm	
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder	
Surface Finish	Matt Smooth	
Colour	White (RAL 9001)	
Width	600 mm	
Height	150 mm	
Net Weight	0.96 kg	

Functional Unit

600 mm Prisma G floor-standing enclosure ComPact INS250 fixed lateral handle vertical 3P 1 direct with long terminal shield 8 0.31 mm

600 mm Prisma G wall-mounted enclosure ComPact INS250 fixed lateral handle vertical 3P 1 direct with long terminal shield 8 0.31 mm

600 mm Prisma G floor-standing enclosure ComPact INS250 fixed lateral handle vertical 4P 1 direct with long terminal shield 8 0.31 mm

600~mm Prisma G wall-mounted enclosure ComPact INS250 fixed lateral handle vertical 4P 1 direct with long terminal shield 8 0.31 mm

 $600~\rm mm$ Prisma G floor-standing enclosure ComPact INV250 fixed lateral handle vertical 3P 1 direct with long terminal shield 8 0.31 mm

600 mm Prisma G wall-mounted enclosure ComPact INV250 fixed lateral handle vertical 3P 1 direct with long terminal shield 8 0.31 mm

 $600~\rm mm$ Prisma G floor-standing enclosure ComPact INV250 fixed lateral handle vertical 4P 1 direct with long terminal shield 8 0.31 mm

600~mm Prisma G wall-mounted enclosure ComPact INV250 fixed lateral handle vertical 4P 1 direct with long terminal shield 8 0.31 mm

600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX100...160 without fixed motor mechanism horizontal 3P 1 direct with long terminal shield 4 0.31 mm

600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX100...160 without fixed motor mechanism horizontal 3P 1 direct with long terminal shield 4 0.31 mm

600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX100...160 without plug-in toggle horizontal 3P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX100...160 without plug-in toggle horizontal 3P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX100...160 without fixed motor mechanism horizontal 4P 1 direct with long terminal shield 4 0.31

600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX100...160 without fixed motor mechanism horizontal 4P 1 direct with long terminal shield 4 0.31 mm

600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX100...160 without plug-in toggle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX100...160 without plug-in toggle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX250 without fixed motor mechanism horizontal 3P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX250 without fixed motor mechanism horizontal 3P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX250 without plug-in toggle horizontal 3P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX250 without plug-in toggle horizontal 3P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX250 without fixed motor mechanism horizontal 4P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX250 without fixed motor mechanism horizontal 4P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G floor-standing enclosure + duct ComPact NSX250 without plug-in toggle horizontal 4P 1 direct with long terminal shield 4 0.31 mm 600 + 300 mm Prisma G wall-mounted enclosure + duct ComPact NSX250 without plug-in toggle horizontal 4P 1 direct with long terminal shield 4 0.31 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	18.500 cm
Package 1 Length	47.000 cm
Package 1 Weight	990.000 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	20
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	20.320 kg

Unit Type Of Package 3	P12
Number Of Units In Package 3	40
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	40.640 kg



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile