
Product datasheet

Specifications





MOUNTING PLATE NSX/CVS 630 V. FIXED ROT.HANDLE

03081

! Discontinued on: 19 May 2023

Price: 1,371.10 ZAR

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G duct
Installation Description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm
Installed Device	EasyPact: fixed CVS400 without earth leakage protection - control: direct front rotary handle - vertical installation EasyPact: fixed CVS630 without earth leakage protection - control: direct front rotary handle - vertical installation ComPact: fixed NSX400 without earth leakage protection - control: direct front rotary handle - vertical installation ComPact: fixed NSX630 without earth leakage protection - control: direct front rotary handle - vertical installation
Poles Description	1 x 3P: fixed CVS400 vertical installation 1 x 4P: fixed CVS400 vertical installation 1 x 3P: fixed CVS630 vertical installation 1 x 4P: fixed CVS630 vertical installation 1 x 3P: fixed NSX400 vertical installation 1 x 4P: fixed NSX400 vertical installation 1 x 3P: fixed NSX630 vertical installation 1 x 4P: fixed NSX630 vertical installation 1 x 4P: fixed NSX630 vertical installation
Condition Of Using Cable Tie	Need additional plate (1M high) when installation of device is in vertical
Number Of Vertical Modules [50 Mm]	12 module(s): CVS400 without earth leakage protection, direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure) 12 module(s): CVS400 without earth leakage protection, direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure) 12 module(s): CVS630 without earth leakage protection, direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure) 12 module(s): CVS630 without earth leakage protection, direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure) 12 module(s): NSX400 without earth leakage protection, direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure) 12 module(s): NSX400 without earth leakage protection, direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure) 12 module(s): NSX630 without earth leakage protection, direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure) 12 module(s): NSX630 without earth leakage protection, direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Standards	IEC 61439-2
Product Certifications	ASEFA

Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Smooth Matt
Colour	White (RAL 9001)
Width	300 mm
Height	400 mm
Net Weight	0.62 kg

Functional Unit

300 mm Prisma G floor-standing duct EasyPact CVS400 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 191 mm 300 mm Prisma G wall-mounted duct EasyPact CVS400 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 191 mm 300 mm Prisma G floor-standing duct EasyPact CVS400 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12 191 mm 300 mm Prisma G wall-mounted duct EasyPact CVS400 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12 191 mm 300 mm Prisma G floor-standing duct EasyPact CVS630 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 191 mm 300 mm Prisma G wall-mounted duct EasyPact CVS630 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 191 mm 300 mm Prisma G floor-standing duct EasyPact CVS630 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12 191 mm 300 mm Prisma G wall-mounted duct EasyPact CVS630 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12 191 mm 300 mm Prisma G floor-standing duct ComPact NSX400 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 191 mm 300 mm Prisma G wall-mounted duct ComPact NSX400 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 191 mm 300 mm Prisma G floor-standing duct ComPact NSX400 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12 191 mm 300 mm Prisma G wall-mounted duct ComPact NSX400 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12 191 mm 300 mm Prisma G floor-standing duct ComPact NSX630 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 191 mm 300 mm Prisma G wall-mounted duct ComPact NSX630 without fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 191 mm 300 mm Prisma G floor-standing duct ComPact NSX630 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12 191 mm 300 mm Prisma G wall-mounted duct ComPact NSX630 without fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12 191 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.500 cm
Package 1 Width	22.000 cm
Package 1 Length	23.000 cm
Package 1 Weight	620.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	10
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	6.480 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
Ø	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile