# **Product datasheet**





# FRONT PLATE CVS250 **VERTICAL FIXED TOGGLE W300** 9M

03250

! Discontinued on: 15 Jun 2023

(!) Discontinued

Price: 757.07 ZAR

# Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G duct Prisma Prisma Pack 250 duct
Type Of Front Plate	Cut-out
Installed Device	EasyPact: fixed CVS100160 without earth leakage protection - control: toggle - vertical installation EasyPact: fixed CVS250 without earth leakage protection - control: toggle - vertical installation
Poles Description	1 x 3P: mounting plate support: CVS100160 vertical installation 1 x 4P: mounting plate support: CVS100160 vertical installation 1 x 3P: mounting plate support: CVS250 vertical installation 1 x 4P: mounting plate support: CVS250 vertical installation
Operating Position	Vertical

# Complementary

Enclosure/Cubicle Description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Pack enclosure - width 300 mm
Connection Position	Direct connection
Number Of Vertical Modules [50 Mm]	9
Standards	IEC 61439-1 IEC 61439-2
Product Certifications	ASEFA
Material	Steel
Surface Finish	Matt Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	450 mm
Width	300 mm
Net Weight	0.98 kg
Quantity Per Set	Set of 1

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Functional Unit	300 mm Prisma G floor-standing duct EasyPact CVS100160 without fixed toggle
	vertical 3P 1 direct with long terminal shield 9

300 mm Prisma G wall-mounted duct EasyPact CVS100...160 without fixed toggle vertical 3P 1 direct with long terminal shield 9

300 mm Prisma G floor-standing duct EasyPact CVS100...160 without fixed toggle vertical 4P 1 direct with long terminal shield 9

300 mm Prisma G wall-mounted duct EasyPact CVS100...160 without fixed toggle

vertical 4P 1 direct with long terminal shield 9
300 mm Prisma Pack 250 Pack enclosure EasyPact CVS100...160 without fixed

toggle vertical 3P 1 direct with long terminal shield 9 300 mm Prisma Pack 250 Pack enclosure EasyPact CVS100...160 without fixed

toggle vertical 4P 1 direct with long terminal shield 9
300 mm Prisma G floor-standing duct EasyPact CVS250 without fixed toggle vertical

3P 1 direct with long terminal shield 9
300 mm Prisma G wall-mounted duct EasyPact CVS250 without fixed toggle vertical

3P 1 direct with long terminal shield 9
300 mm Prisma G floor-standing duct EasyPact CVS250 without fixed toggle vertical

4P 1 direct with long terminal shield 9
300 mm Prisma G wall-mounted duct EasyPact CVS250 without fixed toggle vertical
4P 1 direct with long terminal shield 9

300 mm Prisma Pack 250 Pack enclosure EasyPact CVS250 without fixed toggle vertical 3P 1 direct with long terminal shield 9

 $300~\rm mm$  Prisma Pack  $250~\rm Pack$  enclosure EasyPact CVS250 without fixed toggle vertical 4P 1 direct with long terminal shield 9

#### **Environment**

Ip Degree Of Protection IP30

### **Packing Units**

r acking critis	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	26.0 cm
Package 1 Length	47.0 cm
Package 1 Weight	980.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	17.0 cm
Package 2 Width	27.0 cm
Package 2 Length	53.0 cm
Package 2 Weight	10.24 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	240
Package 3 Height	82.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	257.76 kg



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Halogen Free Plastic Parts Product

### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile