Product datasheet

Specifications





PLAIN FRONT PLATE W300 9M

03817

Discontinued on: 15 Jun 2023

Price: 736.11 ZAR

Main

Range	Prisma	
Range Of Product	Prisma G Prisma P	
Product Or Component Type	Front plate	
Accessory / Separate Part Category	Installation accessory	
Range Compatibility	Prisma Prisma G duct Prisma Prisma P cubicle	
Type Of Front Plate	Plain	
Installed Device	Power meters: kilowatt-hour meters - vertical installation	
Poles Description	ription 1 x 4P: mounting plate support: kilowatt-hour meters vertical installation	

Complementary

Enclosure/Cubicle Description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Cubicle duct - width 400 mm depth 400 mm
Number Of Vertical Modules [50 Mm]	9
Standards	IEC 61439-1 IEC 61439-2
Product Certifications	ASEFA
Material	Steel
Surface Finish	Smooth Matt
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	450 mm
Width	250 mm
Net Weight	1 kg
Quantity Per Set	Set of 1
Functional Unit	400 mm 400 mm Prisma P cubicle 300 mm Prisma G floor-standing duct power meters kilowatt-hour meters vertical 4P 1 9 300 mm Prisma G wall-mounted duct power meters kilowatt-hour meters vertical 4P

Packing Units

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

19

PCE
1
2.500 cm
26.500 cm
46.000 cm
999.000 g
CAR
10
16.800 cm
27.700 cm
52.600 cm
10.300 kg
P12
300
93.000 cm
80.000 cm
120.000 cm
315.960 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile