
Product datasheet

Specifications

Green Premium"



LINERGY LGYE PROFILE 1250A FOR A VERTICAL INSTALLATION LENGTH 1670MM

Discontinued on: 17 Jan 2022

(!) End-of-service on: 17 Dec 2022

Price: 3,255.48 ZAR

Main

Range	Linergy
Range Of Product	Linergy
Product Or Component Type	Profile busbar
Product Name	Linergy LGY
Range Compatibility	Prisma Prisma P enclosure
Busbar Description	Linergy
Quantity Per Set	Set of 1

04505

Complementary

Installation Direction	Vertical, operating position: rear Vertical, operating position: lateral
Installation Description	Cubicle - width 650 mm Cubicle - width 650 + 150 mm
[Ui] Rated Insulation Voltage	1000 V
[Uimp] Rated Impulse Withstand Voltage	12 kV (degree of pollution: 3)
[Ie] Rated Operational Current	1250 A
[Icw] Rated Short-Time Withstand Current	25 kA (1 s) for 3 supports (rear position) 30 kA (1 s) for 4 supports (rear position) 40 kA (1 s) for 3 supports (lateral position) 40 kA (1 s) for 5 supports (rear position) 50 kA (1 s) for 4 supports (lateral position) 60 kA (1 s) for 5 supports (lateral position) 50 kA (1 s) for 7 supports (rear position)
Permissible Current	1290 A at 35 °C: <= IP31 1170 A at 35 °C: > IP31
Busbar Cross Section	32.5 x 42.5 mm
Length	1670 mm
Net Weight	3.38 kg
Type Of Busbar Connection	Single t-slot
Connection Pitch	Free connection position

Environment

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Standards	IEC 61439-2 IEC 61439-1	
Product Certifications	ASEFA	
Packing Units		
Unit Type Of Package 1	PCE	

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information