Product datasheet

Specifications

 Green Premium[™]



PLAIN DOOR W600 6M PRISMA G IP30

08122

() Discontinued on: 15 Jun 2023

Price: 1,309.69 ZAR

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Door
Range Compatibility	Prisma Prisma G enclosure
Provided Equipment	door handle keylock (key 405) other keylock and insert to be ordered separately 2 hinge
Type Of Door	Plain
Ip Degree Of Protection	IP43 with door, canopy and IP43 gasket IP30 without door IP40 with door IP41 with door and canopy

Complementary

Installation Description	Wall-mounted enclosure - width 600 mm Extension enclosure - width 600 mm
Door Opening Side	Reversible
Number Of Locks	1
Door Opening Angle	130 °
Number Of Vertical Modules [50 Mm]	6
Enclosure Material	Handle: polyamide Cover frame: treated sheet steel
Quantity Per Set	Set of 1
Height	330 mm
Width	600 mm
Depth	36 mm
Net Weight	2.6 kg
Surface Finish	Smooth Matt
Colour	White (RAL 9001)

Environment

Ik Degree Of Protection

IK08 conforming to EN/IEC 62262

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Standards	IEC 61439-2 IEC 61439-1

Protective Treatment

Electrophoresis treatment and hot-polymerised polyester epoxy powder

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	36.5 cm
Package 1 Length	64.0 cm
Package 1 Weight	3.11 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	45
Package 2 Height	97.5 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	151.95 kg

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile