# **Product datasheet**





# **EXTENSION FLOOR-STANDING ENCLOSURE W600 33M PRISMA** G IP30

08214

Discontinued on: 15 Jun 2023



#### Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Enclosure extension
Product Compatibility	Floor-standing enclosure - width 300 mm Floor-standing enclosure - width 850 mm
Device Application	Low voltage electrical distribution
Enclosure Type	Functional enclosure delivered in kit form
Enclosure/Cubicle Description	Floor-standing enclosure - width 600 mm
Enclosure Mounting	Surface
Additional Information	Can be combined side by side
Type Of Front Plate	Without to be ordered separately
Number Of Vertical Modules [50 Mm]	33
Number Of 18 Mm Modules Per Row	24
Standards	IEC 61439-1 IEC 61439-2 IEC 62208

### Complementary

[Ui] Rated Insulation Voltage	1000 V on main rear busbars conforming to IEC 61439-2
Network Frequency	50/60 Hz
[In] Rated Current	630 A at 40 °C conforming to IEC 61439-2
[Icw] Rated Short-Time Withstand Current	25 kA 1 s conforming to IEC 61439-2
[lpk] Rated Peak Withstand Current	53 kA conforming to IEC 61439-2
Electrical Insulation Class	Class I
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Smooth Matt
Colour	White (RAL 9001)
Width	600 mm
Height	1830 mm with plinth:
Depth	205 mm
Net Weight	24 kg

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Quantity Per Set	Set of 1
Quantity Per Set	Set of 1

### **Environment**

Ip Degree Of Protection	IP43 with door, canopy and IP43 gasket IP30 without door IP40 with door IP41 with door and canopy	
Ik Degree Of Protection	IK07 without door conforming to EN/IEC 62262 IK08 with door	
Mechanical Robustness	Seismic tests - 2.5G conforming to IEC 60068-2-57	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	64.5 cm
Package 1 Length	188.0 cm
Package 1 Weight	23.55 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	20
Package 2 Height	110 cm
Package 2 Width	200 cm
Package 2 Length	126 cm
Package 2 Weight	480 kg



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>Ø</b>	Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile