



Main

Range	Prisma
Product name	Prisma G
IP degree of protection	IP55 with door
Product or component type	Rear panel Door
Enclosure type	Functional enclosure delivered in kit form
Device application	Low voltage electrical distribution
Enclosure mounting	Surface
Type of front plate	Without
Number of vertical modules [50 mm]	11
Number of 18 mm modules per row	10
Provided equipment	Door for enclosure (x1)

Complementary

Installation description	Wall-mounted duct - width 300 mm
[Ui] rated insulation voltage	1000 V
[In] rated current	630 A at 40 °C conforming to IEC 61439-2
Enclosure material	Rear panel : treated sheet steel Door : treated sheet steel
Additional information	Can be combined side by side and one on top of another
Quantity per set	Set of 1
Height	650 mm
Width	300 mm
Depth	260 mm
Product weight	11.84 kg
Surface finish	Smooth Matt
Colour	White RAL 9001

Environment

IK degree of protection	IK10 with door conforming to EN/IEC 62262
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Standards	IEC 61439-1 IEC 61439-2 IEC 62208
Mechanical robustness	Seismic tests : 2.5G conforming to IEC 60068-2-57

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0930 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------