



Main

Range	Prisma
Product name	Prisma P
IP degree of protection	IP30
Product or component type	Door
Enclosure mounting	Floor-standing
Type of door	Plain
Provided equipment	Door Handle Keylock (key 405) Other keylock and insert (to be ordered separately) Hinge (x2)

Complementary

Door opening side	Reversible
Number of locks	2
Door opening angle	120 °
Installation description	Cubicle - width 400 mm
Number of vertical modules [50 mm]	36
Enclosure material	Treated sheet steel
Quantity per set	Set of 1
Height	2000 mm
Width	400 mm
Depth	30 mm
Product weight	12.44 kg
Surface finish	Smooth Matt
Colour	White RAL 9001

Environment

IK degree of protection	IK08 conforming to EN/IEC 62262
-------------------------	---------------------------------

Standards	IEC 61439-1 IEC 61439-2
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0813 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------