



Main

Range	Prisma
Product name	Prisma P
IP degree of protection	IP55
Product or component type	Door
Enclosure mounting	Floor-standing
Type of door	Transparent
Provided equipment	Door Handle Keylock (key 405) Other keylock and insert (to be ordered separately) Barrier 150 mm for the side compartment Finishing accessory Polyurethane joint Hinge (x4)

Complementary

Door opening side	Reversible
Number of locks	3
Door opening angle	120 °
Installation description	Cubicle - width 650 + 150 mm Cubicle - width 800 mm
Number of vertical modules [50 mm]	36
Enclosure material	Treated sheet steel Glass
Quantity per set	Set of 1
Height	2000 mm
Width	800 mm
Depth	30 mm
Product weight	30.98 kg
Surface finish	Matt Smooth
Colour	White RAL 9001

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

IK degree of protection	IK10 conforming to EN/IEC 62262
Standards	IEC 61439-1 IEC 61439-2
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0827 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------