



### Main

Range	Kaedra
Product or component type	Weatherproof enclosure
Enclosure type	Enclosure for modular device
Accessories included with enclosure	1 terminal block support 2 terminal block 32 holes 3 marking kits 3 wiring straps

### Complementary

Enclosure mounting	Surface
Number of 18 mm modules per row	12
Total number of 18 mm modules	36
Number of horizontal rows	3
Electrical insulation class	Class II Double insulation
Provided equipment	3 marking kit 3 wiring strap 1 terminal block support 2 terminal block 32 holes
Type of front cover	Reversible Transparent
[In] rated current	125 A
Type of rail	DIN
Number of pre-cutouts PG ISO	17
Number of terminal blocks	2 with 32 outgoers
Distribution block outgoers	32 x 10 mm <sup>2</sup> 32 x 16 mm <sup>2</sup>
Locking options description	Optional keylock
Enclosure material	Self-extinguishing polymer
Width	340 mm
Height	610 mm
Depth	160 mm
Colour	Door : transparent green Enclosure : light grey ( RAL 7035 )

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Standards	EN 50102 EN 50262 IEC 60439-3 IEC 60529 IEC 60695-2-1 IEC 670
Fire resistance	650 °C conforming to IEC 60695-2-1
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 50102
Environmental characteristics (UV)	UV resistant class 3 conforming to ISO 4582 2010 Ultraviolet degradation test conforming to ISO 4892-2 2013
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C

## Contractual warranty

Warranty period	18 months
-----------------	-----------