Product datasheet

Specification





Kaedra - for modular device with interface - 2 x 12 modules - 2 terminal blocks

13439

Price: 2,091.76 ZAR

Main

Range	Mureva
Product Name	Mureva Enclosure
Product Or Component Type	Weatherproof enclosure
Enclosure Type	Enclosure for modular device with interface
Mounting Plate Description	Slotted

Complementary

Complementary	
Enclosure Mounting	Surface
9 Mm Pitches	24
Number Of 18 Mm Modules Per Row	12
Total Number Of 18 Mm Modules	24
Number Of Horizontal Rows	2
Electrical Insulation Class	Double insulation Class II
Number Of Openings Of Interface	3
Number Of Plates	1 for 65 x 85 power outlets 3 for push-button controls
Provided Equipment	2 marking kit 2 wiring strap 1 plate for 65 x 85 power outlet 3 plate for push-button control 1 terminal block support 2 terminal block 22 holes
Type Of Front Cover	Reversible Transparent
[In] Rated Current	90 A
Type Of Rail	DIN
Number Of Pre-Cutouts Pg Iso	17
Number Of Terminal Blocks	2 earth / neutral (screw connection) with 22 outgoers
Distribution Block Outgoers	22 x 10 mm ² 22 x 16 mm ²
Locking Options Description	Optional keylock
Enclosure Material	Self-extinguishing polymer
Base Dimension	90 x 100 mm
Width	448 mm

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Height	460 mm
Depth	160 mm
Internal Depth	88 mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)

Environment

Standards	IEC 60670 IEC 61439-3 EN 50262 IEC 60695-2-1	
Fire Resistance	650 °C conforming to IEC 60695-2-1	
Ip Degree Of Protection	IP65 conforming to IEC 60529	
Ik Degree Of Protection	IK09 conforming to EN 50102	
Environmental Characteristics (Uv)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013	
Overvoltage Category	II .	
Ambient Air Temperature For Operation	-2560 °C	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.000 cm
Package 1 Width	47.000 cm
Package 1 Length	47.500 cm
Package 1 Weight	4.250 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	18
Package 2 Height	80.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	87.240 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >








Lower Impact Materials Transparency RoHS/REACh

Resource performance



26

Well-being performance





Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations