

Product datasheet

Specifications



Concept processor 80186 Modicon Quantum - 1 Modbus plus, 2 Modbus RS232

140CPU11303

⚠ Discontinued - Service only

⚠ Discontinued on: 31 May 2015

⚠ End-of-service on: 31 Dec 2023

Price: 119,291.50 ZAR

Main

Range Of Product	Modicon Quantum automation platform
Product Or Component Type	Processor
Software Name	ProWORX 32 Concept
Processor Name	80186
Mathematical Coprocessor	Without

Complementary

Clock Frequency	20 MHz
Memory Description	Internal RAM 368 kB
Exact Time For 1 Kinstruction	0.3...1.4 ms LL984
Watchdog Timer	250 ms
Clock Drift	+/-8 s/day at 0...60 °C
I/O Words	30 I/32 O distributed 64 I/64 O max local 64 I/64 O remote
I/O Words/Network	500 I/500 O distributed
Drops/Network	63 distributed
Number Of Drops	31 remote
Number Of Network	2 remote 3 distributed
Battery Type	Lithium 7 µA 210 µA
Battery Capacity	1.2 Ah
Battery Life	10 year(s)
Number Of Port	1 Modbus RS232 1 Modbus Plus
Communication Module Processor Capacity	2 NOM, NOE, CR, NMS
Switch Function	Without key switch
Marking	CE
Bus Current Requirement	790 mA
Module Format	Standard

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Net Weight	0.3 kg
------------	--------

Environment

Product Certifications	FM Class 1 Division 2 cUL
Standards	UL 508 CSA C22.2 No 142
Resistance To Electrostatic Discharge	4 kV contact conforming to IEC 801-2 8 kV on air conforming to IEC 801-2
Resistance To Electromagnetic Fields	10 V/m 80...2000 MHz conforming to IEC 801-3
Ambient Air Temperature For Operation	0...60 °C
Ambient Air Temperature For Storage	-40...85 °C
Relative Humidity	95 % without condensation
Operating Altitude	<= 5000 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5 cm
Package 1 Width	16.5 cm
Package 1 Length	31 cm
Package 1 Weight	514 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	7
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.113 kg
Unit Type Of Package 3	S04
Number Of Units In Package 3	21
Package 3 Height	30 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	11.827 kg


Contractual warranty

Warranty	18 months
----------	-----------

Dimensions Drawings

Racks for Modules Mounting

Dimensions of Modules and Racks



- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots