# **Product datasheet**

Specification





# 140CRA31200 - Quantum RIO Drop E/IP 1CH

140CRA31200

- ! Discontinued on: 31 Dec 2022
- ! To be end-of-service on: 31 Dec 2030

① To be discontinued

Price: 41,327.35 ZAR

## Main

Range Of Product	Modicon Quantum	
Product Or Component Type	Ethernet RIO drop adaptor	
Number Of Port	3	
Integrated Connection Type	Ethernet IP/Modbus TCP for service port Ethernet IP/Modbus TCP for device network	
Communication Port Protocol	Ethernet IP/Modbus TCP	
Communication Service	The input data are collected and published to the remote I/O head adaptor Output modules are updated with the data received from remote I/O head adaptor	

## Complementary

Topology	Daisy chain loop	
Local Signalling	1 LED (green/red) for module status (Mod Status) 1 LED (green/red) for network communication status (Net Status) 1 LED (green) for RUN 1 LED (red) for I/O	
Product Compatibility	140CRP31200	
Environmental Characteristic	Standard environment Hazardous location class I division 2 conforming to EN/IEC 61131-1	
Width	167 mm	
Height	50 mm	
Net Weight	0.554 kg	

#### **Environment**

Product Certifications	CE
	UL 508
	C-Tick
Standards	IEC 55011
	CSA C22.2 No 142
	IEC 61000-4-16
Ip Degree Of Protection	IP20 conforming to IEC 61131-2
	IP20 conforming to IEC 60527
Overvoltage Category	Class I conforming to IEC 61131-2
Ambient Air Temperature For	060 °C conforming to IEC 60068-2-2
Operation	060 °C conforming to IEC 60068-2-2
Ambient Air Temperature For	-4085 °C conforming to IEC 60068-2-2
Storage	-4085 °C conforming to IEC 60068-2-2

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Vibration Resistance	3.5 mm constant amplitude (f= 0.58.4 Hz) conforming to IEC 61131-2 1 gn constant acceleration (f= 8.4150 Hz) conforming to IEC 61131-2
Operating Altitude	2000 m
Maximum Altitude Transport	3000 m
Relative Humidity	93 % conforming to IEC 60068

# Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.900 cm
Package 1 Width	16.400 cm
Package 1 Length	31.300 cm
Package 1 Weight	593.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	7
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.650 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

## Well-being performance

<b>②</b>	Reach Free Of Svhc	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes


#### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

## **Dimensions Drawings**

## **Racks for Modules Mounting**

#### **Dimensions of Modules and Racks**



- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots