# **Product datasheet**

Specifications





## Ethernet network TCP/IP module class B30 - data editor, rack viewer

140NOE77101C

() Discontinued on: 31 Dec 2018

() To be end-of-service on: 31 Dec 2026

## Price: 52,187.73 ZAR

### Main

Modicon Quantum automation platform
Ethernet network TCP/IP module
Transparent Ready
Class B30
Rack viewer Diagnostics via predefined web pages Data Editor (via PC terminal)
Modbus TCP messaging SNMP network management Global Data Bandwidth management FDR server I/O scanning
Ethernet Modbus TCP/IP
MT/RJ - 100BASE-FX fiber optic RJ45 - 10BASE-T/100BASE-TX twisted pair
10/100 Mbit/s

## Complementary

Redundancy	Yes hot standby redundant architecture	
Supply	Via the power supply of the rack	
Marking	CE	
Local Signalling	1 LED for 10 Mbps or 100 Mbps data rate (10 MB/100 MB)	
	1 LED for collision detection (Coll)	
	1 LED for download mode (Kernel)	
	1 LED for Ethernet module fault (Fault)	
	1 LED for Ethernet network status (RUN)	
	1 LED for full-duplex mode (Fduplex)	
	1 LED for module ready (Ready)	
	1 LED for network active (Link)	
	1 LED for rack operational (Active)	
	1 LED for transmission/reception activity (TxAct/RxAct)	
Current Consumption	750 mA at 5 V DC	
Module Format	Standard	
Net Weight	0.345 kg	

### Environment

Ip Degree Of Protection

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

IP20

Product Certifications	UL 508
	cUL
Standards	FM Class 1 Division 2 CSA C22.2 No 142
Protective Treatment	Conformal coating Humiseal 1A33
Resistance To Electrostatic Discharge	4 kV contact conforming to IEC 801-2 8 kV on air conforming to IEC 801-2
Resistance To Electromagnetic Fields	10 V/m 801000 MHz conforming to IEC 801-3
Ambient Air Temperature For Operation	0°.000
Ambient Air Temperature For Storage	-4085 °C
Relative Humidity	95 % without condensation
Operating Altitude	<= 4500 m

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	16.5 cm
Package 1 Length	31.0 cm
Package 1 Weight	587.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	7
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.624 kg

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh


### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
Circularity Profile	End of Life Information

#### **Dimensions Drawings**

#### **Racks for Modules Mounting**

#### **Dimensions of Modules and Racks**



- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots