Product datasheet

Specification





Reflex iC60N Ti24 25 A 2P curve C integrated control MCB

A9C62225

Price: 7,730.19 ZAR

Main

Device Application	Distribution Control	
Range	Acti9	
Product Name	Reflex iC60	
Device Short Name	Reflex iC60N	
Product Or Component Type	Integrated control circuit breaker	
Poles Description	2P	
Number Of Protected Poles	2	
Network Type	AC	
Trip Unit Technology	Thermal-magnetic	
Curve Code	С	

Complementary

J J	
[In] Rated Current	25 A
Network Frequency	50/60 Hz
Breaking Capacity Code	N
Breaking Capacity	20 kA Icu at 220240 V AC 50/60 Hz conforming to EN/IEC 60947-2 10 kA Icu at 380415 V AC 50/60 Hz conforming to EN/IEC 60947-2
[Ui] Rated Insulation Voltage	500 V AC
Contact Position Indicator	Yes
Control Type	ON/OFF button Toggle Remote control by pulse Remote control by continuous command
Control Signal Type	Maintained very low voltage Maintained Impulse
Local Signalling	Green LED: device ON Red LED: fault Flashing LED: device overheat Flashing LED: device tripped Flashing LED: device ready
[Uc] Control Circuit Voltage	230 V AC 50/60 Hz 24 V AC 50/60 Hz 48 V AC 50/60 Hz 24 V DC 48 V DC
[Us] Rated Supply Voltage	230 V AC at 50/60 Hz
Mounting Mode	Fixed

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Mounting Support	35 mm symmetrical DIN rail	
9 Mm Pitches	9	
Height	84 mm	
Width	81 mm	
Depth	77 mm	
Colour	White	
Mechanical Durability	50000 cycles	
Electrical Durability	AC-1: 50000 cycles AC 50 Hz	
Provision For Padlocking	Padlockable	
Locking Options Description	Padlock in OFF position	
Earth-Leakage Protection	Protection Separate block	
Product Compatibility	With PLC	

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529	
Pollution Degree	3	
Tropicalisation	2	
Relative Humidity	93 % at 40 °C	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	11.2 cm
Package 1 Length	16.5 cm
Package 1 Weight	582.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	14
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	8.611 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Mercury Free	
⊘	Rohs Exemption Information	Yes
⊘	Halogen Free Plastic Parts Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information