## **Product datasheet**

Specifications





# Reflex iC60N Ti24 25 A 3P curve C integrated control MCB

A9C62325

## Price: 7,962.06 ZAR

#### Main

Device Application	Distribution Control
Range	Acti9
Product Name	Reflex iC60
Device Short Name	Reflex iC60N
Product Or Component Type	Integrated control circuit breaker
Poles Description	3P
Number Of Protected Poles	3
Network Type	AC
Trip Unit Technology	Thermal-magnetic
Curve Code	C

## Complementary

25 A
50/60 Hz
Ν
20 kA lcu at 220240 V AC 50/60 Hz conforming to EN/IEC 60947-2 10 kA lcu at 380415 V AC 50/60 Hz conforming to EN/IEC 60947-2
500 V AC
Yes
ON/OFF button Remote control by pulse Remote control by continuous command Toggle
Maintained Impulse Maintained very low voltage
Flashing LED: device overheat Green LED: device ON Flashing LED: device tripped Flashing LED: device ready Red LED: fault
230 V AC 50/60 Hz 24 V AC 50/60 Hz 48 V AC 50/60 Hz 24 V DC 48 V DC
230 V AC at 50/60 Hz
Fixed

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	11
Height	84 mm
Width	99 mm
Depth	77 mm
Colour	White
Mechanical Durability	50000 cycles
Electrical Durability	AC-1: 50000 cycles AC 50 Hz
Provision For Padlocking	Padlockable
Locking Options Description	Padlock in OFF position
Earth-Leakage Protection	Separate block
Product Compatibility	With PLC

## Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529	
Pollution Degree	3	
Tropicalisation	2	
Relative Humidity	93 % at 40 °C	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.000 cm
Package 1 Width	11.200 cm
Package 1 Length	16.500 cm
Package 1 Weight	698.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	14
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	10.249 kg

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Halogen Free Plastic Parts Product

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information