

# Product datasheet

Specifications



## Acti9 - RCA remote ctrl aux for iC60 1P-1PN-2P

A9C70112

Price: 5,650.86 ZAR

### Main

Range Of Product	Acti9
Product Or Component Type	Remote control auxiliary
Device Short Name	RCA iC60
Signal Contacts Composition	1 OF volt-free contacts
Signalling Circuit Voltage	Volt-free contact 24...230 V 0.01...1 A AC

### Complementary

Control Type	Remote control impulse and maintained 230 V AC 50/60 Hz
Input Current	5 mA impulse 5 mA maintained
Impulse Duration	>= 200 ms control circuit
Response Time	< 500 ms
[Us] Rated Supply Voltage	230 V AC 50/60 Hz
Power Consumption In W	1 W
[Ui] Rated Insulation Voltage	400 V
[Uimp] Rated Impulse Withstand Voltage	6 kV
Value Of Setting	Mode A: reclosing authorized after tripping Mode B: reclosing inhibited after tripping Auto: remote control authorized Off: remote control inhibited
Local Signalling	Flashing green LED: ready to operate Flashing orange LED: not operational
Mounting Mode	Fixed
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	NO
9 Mm Pitches	7
Height	93 mm
Width	63 mm
Depth	75.5 mm
Net Weight	400 g
Colour	White
Electrical Durability	10000 cycles
Mechanical Durability	10000 cycles

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Provision For Padlocking	Padlockable
Wire Stripping Length	Power supply: 10 mm for bottom connection Input: 10 mm for bottom connection Output: 8 mm for top connection
Tightening Torque	Power supply: 1 N.m Input: 1 N.m Auxiliary output: 0.7 N.m
Range Compatibility	Acti 9 Acti9 iC60 Acti 9 Acti9 iC65 Acti 9 iMDU voltage adaptor
Product Compatibility	1P + N iC60 2P iC60 1P iC60 1P iC65 2P iC65 iMDU

## Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution Degree	3 conforming to IEC 60947
Overvoltage Category	II
Tropicalisation	2
Relative Humidity	93 % at 40 °C
Ambient Air Temperature For Storage	-40...70 °C
Ambient Air Temperature For Operation	-25...60 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.000 cm
Package 1 Width	11.000 cm
Package 1 Length	16.200 cm
Package 1 Weight	496.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	14
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	7.200 kg

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.




[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
 Halogen Free Plastic Parts Product	

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>