

Product datasheet

Specifications



Pump - DP Control, 208-230V, 50/60Hz

ACAC10031

⚠ Discontinued on: 08 Mar 2022

⚠ To be end-of-service on: 15 Mar 2032

⚠ Discontinued - Service only

Price: 41,822.18 ZAR

Overview

Lead Time	Special Order - Call for Quoted Lead Times
-----------	--

General

Maximum Recommended Flowrate	1.39 l/s
Tube Material	Copper
Pressure Rating	1599.58 kPa

Physical

Length	0.91 m
Tube Diameter	25.40 mm
Net Weight	13 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.7 cm
Package 1 Width	73.7 cm
Package 1 Length	73.7 cm
Package 1 Weight	13 kg

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
-------------------	--
