

Product datasheet

Specifications



InRow RD, 300mm, Fluid Cooled, 220-240V, 50Hz

ACRD201

Overview

Lead Time	Special Order - Call for Quoted Lead Times
-----------	--

Main

Main Input Voltage	220 V 240 V
Number Of Rack Unit	42U
Provided Equipment	Installation guide Operations and maintenance manual

General

Compressor Type	Scroll
Air Discharge Option	Horizontal
Intake Air Option	Rear return
Air Flow	1080.76 l/s
Condensate Pump Flow	0.01 m3/h

Physical

Colour	Black
Height	199.1 cm
Width	30 cm
Depth	107 cm
Net Weight	199.09 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Power	4400 W
Network Frequency	50 Hz

Conformance

Product Certifications	cUL listed C-Tick CE UL listed
------------------------	---

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Communications & Management

Control Panel	Multifunction LCD status and control console
---------------	--

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	211.8 cm
Package 1 Width	113.7 cm
Package 1 Length	74.6 cm
Package 1 Weight	241.82 kg

Contractual warranty

Warranty	1 year (parts only), 1 year on-site repair or replace with factory authorized Start-Up
----------	--

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope
